



Product Service

Compliance Document

No. D 18 01 98208 006

Holder of Certificate: **Schneider Electric Solar Inverters USA, Inc**
 250 S VASCO RD,
 LIVERMORE CA 94551
 USA

Product: **Converter
 Grid-Connected Inverter**

Model(s): **Conext™ CL-60E**

Parameters:

PV input ratings:	
Min. MPP voltage:	570V DC
Max. MPP voltage:	850V DC
Max. input voltage:	1000V DC
Max. input current:	120A
Isc PV:	140A
AC output ratings:	
Rated output voltage:	3/N/PE AC 400/230V
Rated output frequency:	50/60 Hz
Max. continuous out current:	96 A
Rated output power:	60000 W
Max. apparent power:	66000 VA
Power factor range:	Adj. 0.8 overexcited ... 0.8 underexcited
Protection class:	I
Ingress protection:	IP65(Electronics), IP20(Rear Portion)
Oversvoltage category:	III[MAINS], II[PV]
Ambient temperature:	-25°C ... +60°C

Tested according to: NRS 097-2-1:2017

This Compliance document confirms the compliance with the listed standards on a voluntary basis. It refers only to the sample submitted for testing and certification and does not certify the quality or safety of the serial products. See also notes overleaf.

Test report no.: 701261703501-01

Date, 2018-02-09


 (Zhengdong Ma)



Page 1 of 1